

Features/Benefits

- 6.0 x 6.1 mm dimension
- Height 3.45 mm
- Soft actuator
- Long life 3M cycles
- IP54

Specification

FUNCTION: Momentary action CONTACT ARRANGEMENT: SPDT, NC TERMINALS: SMT termination TRAVEL: 0.3 ± 0.2 mm

Mechanical

OPERATING LIFE: 3,000,000 cycles

Electrical

 $\begin{array}{l} \mbox{VOLTAGE: DC 1V to 16V} \\ \mbox{CURRENT: 10}\mbox{μA} to 50mA \\ \mbox{CONTACT RESISTANCE: 200mΩ max.} \\ \mbox{$500m$\Omega$ max. after testing} \\ \mbox{INSULATION RESISTANCE: 100 MΩ min.} \\ \mbox{DIELECTRIC VOLTAGE: AC 250V} \end{array}$

Typical Applications

- Elevator button & alarm
- Robotic vaccum
- Door handle
- Mower



Environmental

OPERATING TEMPERATURE: -40°C to 90°C STORAGE TEMPERATURE: -40°C to 90°C

Process

SOLDERING: This component is suited to the following methods: Infrared Reflow Soldering in accordance with IEC61760-1


Packaging

1100 pieces per reel

How To Order

Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

For any part number different from those listed above, please consult your local representative.






First Angle Projection Dimensions are shown: mm


Specifications and dimensions subject to change


Ы

٦ آ



0,6±0 Ξ 0.2 В





NEW



