



P.C.B. LAYOUT

INTENSITY 力度									
C	D	E							
160±50	200±50	250±50							
LED COLOR									
1	2	3	4	5	6	12	13	14	23
Red	Yellow	Green	Blue	White	Pure Green	Red Yellow	Red Green	Red Blue	Yellow Green

NO.	PART NAME	MATERIAL	QTY	FINISHING
6	LED		1	
5	CONTACT	SUS	1	AG-PLATED
4	TERMINAL	BRASS	4	AG-PLATED
3	CASE	PA66	1	
2	COVER	PET	1	NATURAL
1	KNOB	PA66	1	

TOLERANCE UNLESS SPECIFIED									
UP TO 5mm: ±0.1	ANGULAR	1							
ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			BY	APPD	
TITLE: TACT SWITCH				UNIT : MM	ROHS COMPLIANT	DWN			
MODEL: TC-1193-L-C				SCALE: 1:1	CHK'D				
HAOYU(HONGKONG)LIMITED						APPD			
						PRO.AGL:			REV :A0