





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司			
				X.X	±0.30			UNIT	mm						
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		PH-00041			
				X.XXX	±0.10			SHEET	1/1	TITLE:		2.54PH H=2.5 2X10P DIP			
				Angle	±3'	APPROVE		PROJ.	◆						
				DIM	TOL										
A	REV	DATE	MODIFICATION DESCRIPTION	CHANGE											
1	2	3	4	5	6	7	8	9							