



线路板开孔尺寸
P.C.B LAYOUT



按点示意图
SCHEMATIC



主要技术特性:

- 1. 额定电负荷: DC 12V, 1A;
- 2. 接触电阻: $\leq 30m\Omega$;
- 3. 绝缘电阻: $\geq 100M\Omega$;
- 4. 耐 压 : AC500V(50-60HZ) 1min;
- 5. 插 拔 力: 2.94-29.4N;
- 6. 寿 命: 5,000次。

主要技术要求

- 1. 未注线性公差:
 - 0.0-10.0mm $\pm 0.20mm$
 - 10.0-20.0mm $\pm 0.25mm$
 - 20.0-50.0mm $\pm 0.30mm$
- 2. 外观应良好, 无锈蚀、裂痕、电镀不良等现象。

Model No.	DC-005-A	DC-005-B
PIN $\phi(X)$	2.0	2.5

6	后 盖	1	PBT	(黑)
5	基 座	1	PBT	(黑)
4	插 针	1	H59黄铜棒	铜锡
3	簧 片	1	锰钢T=0.25	银
2	弯 片	1	H62黄铜带T=0.35	银
1	平 片	1	H62黄铜带T=0.50	银
序号	名 称	数量	材 料	镀 涂

HAOFU ELECTRONCS TECHNOLOGY CO., LTD

COPYRIGHT RESERVED, PLEASE DO NOT COPY.

PART NAME		CONNECTOR		DRAWING		Y,C,ZHANG		DWG.No.		SBICL	
PART NO.		DC-005-X		CHECK		G.C.Chen		REV.		A1	
UNIT :	TOLERANCE OTHERWISE	UP TO 5 ABOVE 5~30 ABOVE 30 ANGLE	± 0.2 ± 0.3 ± 0.5 ± 3	ANGLE	APPROVAL		DATE		14-03-2013		
					SCALE		PAGE		1 OF 1		