


RoHS
Compliant



规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
2.0A
2. 额定电压: Voltage Rating
5V DC
3. 接触阻抗:Contact Resistance
50 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Level
5. 绝缘阻抗:Insulation Resistance:
100MEGA ohms MIN

项次	品名	材质	颜色/电镀	料号	数量
①	FOMA10PIN胶芯	PBT	黑色	A-252-AA	1PCS
②	FOMA10PIN胶芯	c2680	镀金1~3u'	E-005-11	3PCS
③	FOMA10PIN卡钩	SUS		F-011-40	2PCS

HADFU ELECTRONCS TECHNOLOGY CO.,LTD

COPYRIGHT RESERVED,PLEASE DO NOT COPY.

PART NAME		CONNECTOR		DRAWING		Y,C,ZHANG		DWG.No.		SBICL	
PART NO.		FOMA 10PIN		CHECK		G.C.Chen		REV.		A1	
UNIT : mm	TOLERANCE OTHERWISE	UP TO 5	±0.2	ANGLE	APPROVAL	DATE	14-03-2013				
		ABOVE 5~30	±0.3								
		ABOVE 30	±0.5	0°±3'	SCALE	2:1	PAGE		1 OF 1		