





A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME



- TYPE C USB技术要求:
- 电气性能
 - 1.1 额定电流: 3A.
 - 1.2 额定电压: 20V.
 - 1.2 耐压: 500 V(AC) for 1 min.
 - 1.3 接触阻抗: 40mΩ Max. 可靠性和环境测试后阻抗变化不得超过10mΩ.
 - 1.4 绝缘阻抗: 100 MΩ Min.
 - 机械性能
 - 2.1 插入力: 5-20N MAX. 拔出力: 8-20N.
 - 2.2 寿命测试: 10000cycles, 拔出力6-20N.
 - 2.3 推力: 50N min.
 - 2.4 剥离强度: 150N min.
 - 2.5 扭曲强度: 0.75Nm
 - 材料要求
 - 4.1 胶芯材料: LCP
 - 4.2 外壳材料: SUS304
 - 4.3 端子材料: C2680
 - 4.4 盐雾要求: 24H
 - 4.5 工作温度: -20° C-85° C



品赞科技®
G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:
 X. ±0.30
 X.x ±0.20
 X.xx ±0.15
 X.xxx ±0.10
 Angles ±3°

DESIGN FengFengChen	DATE 2021.03.08	Molde code:	
CHECKED	DATE	GT-USB-7060B	
APPROVED	DATE	REV.: X1	SCALE: 4:1
http://www.dg-switch.com		UNIT: mm	
TEL:0769-82388879		SIZE: A4	SHEET: 1/1