


Operating Pressure:200gf±100g
 Operating Stroke:2.2mm±0.3
 Cover:Nylon66,UL rated:94V-2 min
 Base:Nylon66,UL rated:94V-2 min
 Terminal:Brass,silver or tin plated
 Rating:1A 125VAC 0.5A 250VAC
 Function:(ON)-OFF
 Contact Resistance:50mΩ MAX
 Insulation Resistance:100MΩ MIN .
 Dielectric Strength:AC 500V 1 minute
 Electrical life:50,000 cycles
 Operating Temperature:-20°C~85°C
 Safety Approval:



东莞市德松电子有限公司
 DASUNG (DONGGUAN) ELECTRONICS CO.,LTD

公差 TOLERANCES		.X±0.5	.XX±0.3	角度 ANGLE ±1°	单位 UNIT	DIMENSION UNIT		mm.
版本 VERSION	核准 APPROVED BY	A0	核对 CHECKED BY	日期 DATE	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO	
变更说明 CHANGE DESCRIPTION	日期 DATE	ECON NO.				PB26-M13-ZT-N-NN	1080162	
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECON NO.	核准 APPROVED BY	核对 CHECKED BY	日期 DATE	绘图 DRAWN BY	品名 TITLE
						2017.06.30	吴润成	