



### Performance Specifications (性能)

<b>Short-time overload</b>	短时间过负荷	±(0.5%+0.0005Ω) Test method 测试方法: Running under 5 times of rated power in 5 seconds at room temperature. 5 倍额定功率、室温, 持续工作 5 秒 Except for special specifications (see datasheet) (特殊规格除外, 具体详见产品规格书)
<b>Soldering heat</b>	耐焊接热	±(0.5%+0.0005Ω)
<b>Solderability</b>	可焊性	Coverage must be over 95%.
<b>Thermal Shock</b>	热冲击	±(0.5%+0.0005Ω)
<b>Load life</b>	负载寿命	± (1%+0.0005Ω)

### Ordering Procedure (Example:LR12 2W 1% 5mΩ T/R-4000)

订购方式 (例如: LR12 2W 1% 5mΩ T/R-4000)

