



ROHS

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A		新订图面		2016.8.13



Specifications / 技术规格:

Current rating: 1A
 额定电流: 1A
 Voltage rating: 125 V AC,DC
 额定电压: 125V AC, DC
 Insulation Resistance: 500 MΩ Min.
 绝缘电阻: 最小500MΩ
 Dielectric Withstanding: 500V AC 1Min
 耐电压: 500V AC 1分钟
 Contact Resistance: 20mΩ Max.
 接触电阻: 最大20mΩ
 Operating Temperature: -25°C to +85°C
 工作温度: -25°C 到85°C

Materials / 材料:
 Contact Material: Brass (Sn plating)
 接触铜针材料: 黄铜(镀锡)
 Soldering Terminal: Brass (Sn plating)
 焊片材料: 黄铜(镀锡)
 Insulation Material: LCP UL94V-0
 绝缘体材料: LCP UL94 V-0

孔数	型号	尺寸 (mm)		
		A	B	C
2	125-2AWT	1.25	4.30	7.00
3	125-3AWT	2.50	5.55	8.25
4	125-4AWT	3.75	6.80	9.50
5	125-5AWT	5.00	8.05	11.30
6	125-6AWT	6.25	9.30	12.55
16	125-16AWT	18.75	21.80	24.50

东莞市美韩电子科技有限公司
 Dongguan Usakro Electronic Technology Co., Ltd.

GENERAL TOLERANCE

X.* ± 3'	.XXX ± 0.10
.X* ± 2'	.XX ± 0.15
.XX* ± 1'	.X ± 0.25
.XXX* ± 0.5'	X. ± 0.35

DESIGN: WWH

DATE: 2016.8.13

DWG. NO.

CHECKED:

DATE: 2016.8.13

AUDITED:

DATE: 2016.8.13

APPROVED:

DATE: 2016.8.13

PART NO.

UK-1.25-2AWT

TITLE.

1.25卧贴

REV.	UNIT.	SCALE.	MM
A	MM	1:1	