




CIRCUIT



SPECIFICATIONS


规格
 CONTACT RATING: DC5~24V, 1~50mA
 触点额定值: DC5~24V, 1~50mA
 OPERATION LIFE: 3,000,000 cycles
 运行寿命: 300万次循环
 CONTACT RESISTANCE: 100mΩ max
 接触电阻: 最大100mΩ
 INSULATION RESISTANCE: 100MΩ min, 500VDC
 绝缘电阻: 最小100MΩ, 500VDC
 OPERATING TEMPERATURE: -25°C to +70°C
 工作温度: -25°C至+70°C
 Height: 7.5mm
 高度: 7.5毫米
 Operating force: 200±30gf
 操作力: 200±30gf
 Waterproof grade: IP65
 防水等级: IP65



PCB LAYOUT

ITEM	Name	Materials	NUM	COLOR
6	SWITCH HOUSING 开关外壳	Nylon 尼龙	1	
5	SWITCH BUTTON 开关按钮	Nylon 尼龙	1	Brown 棕色
4	COVER PLATE 盖板	SUS 不锈钢	1	
3	SHRAPNEL 弹片	SUS 不锈钢	1	Silver 镀银
2	TERMINAL 端子	Brass 黄铜	4	Silver 镀银
1	SILICONE 硅胶垫圈	Silica gel 硅胶	1	

REV	DATE	REVISION	DESCRIPTION	ISSUE
A4				
A3				
A2				
A1				



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN

MODEL NO: TP160112075
 Https: www.rocpu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission