



- 技术参数值 (Technical Parameters)
- 1.电气额定值 (Electrical Rating) : 1A 250VAC
 - 2.电气寿命 (Electrical lifetime) :Min 10,000 cycles
 - 3.接触电阻 (Contact Resistance) :≤50mΩ
 - 4.操作力 (Operating force) :35±20gf
 - 5.自有位置 (Free position) :10.4±1mm
 - 6.动作位置 (Operating position) :8.7±0.5mm
 - 7.环境温度 (Ambient temperature) :T85°
 - 8.耐压 (Withstand Voltage) :
Between terminal and terminal 500V/5S/5mA;
Between terminals and case 1500/5S/5mA
 - 9.绝缘电阻 (Insulation Resistance) :
≥100MΩ (Test Voltage 500VDC)
 - 10.漏电起痕指数Proof Tracking Index (PTI) : 175V

6	滚轮 Roller	1	POM	黑色 black
5	压柄 Pressing handle	1	不锈钢 SUS	
4	塑盖 Plastic cover	1	PBT	黑色 black
3	动触片组件 Contact parts	1	铍青铜+银丝 Beryllium bronze + silver wire	
2	推动子 Push parts	1	尼龙66 PA66	灰色 grey
1	底座组件 Bottom assembly	1	PBT+黄铜+银丝 PBT + brass + silver wire	
序号 Serial number	零件名称 Part name	数量 quantity	材质 Texture of material	备注 REMARK

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN

MODEL NO: TP30111300
Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission