


Circuit diagram




| | | |
|---|------------------------|-----------------|
| 1 | Rubber shell | PA66 |
| 2 | Seal ring | Silica gel |
| 3 | Base | Brass+PA66 |
| 4 | According to sincerity | Pom |
| 5 | Contact moving plate | Phosphor bronze |
| 6 | Strut | SUS |

Technical Parameters

技术参数

- 1. Electrical Rating: 0.1A 125/250VAC
3A/12VDC; 0.1A/48VDC
- 1. 电气额定值: 0.1A 125/250VAC
3A/12VDC; 0.1A/48VDC
- 2. Electrical lifetime: 100,000 cycles
- 2. 电气寿命: 100,000 cycles
- 3. Mechanical lifetime: 100,000 cycles
- 3. 机械寿命: 100,00 cycles
- 4. Contact Resistance: ≤100mΩ
- 4. 接触电阻: ≤100兆欧
- 5. Operating force: 1.3N MAX
- 5. 操作力: 1.3N MAX
- 6. Pretravel: 0.3~1.0mm
- 6. 动作行程: 0.3~1.0mm
- 7. OP: 6.75±0.2mm
- 7. 动作位置: 6.75±0.2mm
- 8. Withstand Voltage: Feet and Feet 500V/5S/5mA
Feet and Shell 1500/5S/5mA
- 8. 耐压: 脚与脚 500/5s/5mA
脚与壳 1500/5S/5mA
- 9. Insulation Resistance: ≥100MΩ
- 9. 绝缘电阻: ≥100MΩ
- 10. Proof Tracking Index(PTI): 175V
- 10. 漏电起痕指数 (PTI): 175V
- 11. Ambient temperature: 125°
- 11. 环境温度: 125°
- 12. Waterproof grade: IP67
- 12. 防水等级: IP67
- 13. working temperature: -25°C~ + 105°C
- 13. 工作温度: -25°C~ + 105°C

| | | | | |
|-----|------|----------|-------------|-------|
| A4 | | | | |
| A3 | | | | |
| A2 | | | | |
| A1 | | | | |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



| | |
|------------------|--------|
| COMMON TOLERANCE | |
| X.XX | ± 0.10 |
| X.X | ± 0.15 |
| X | ± 0.25 |
| ANGULAR | — |

| | | | | |
|----------|--------|------------|------|-----------------------|
| UNIT | MM | PROJECTED | | PRODUCT NAME: |
| DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP330414000 |
| DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpu.tw |

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission