









修 订	标 记	修 改 描 要	签 名	日 期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DRG		2016-03-12



SPECIFICATIONS
 Current Rating: 2A AC,DC
 Voltage Rating: 100V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 800V AC/minute
 Pin Material: Brass/Gold-flash
 Solder Tabs: Brass/Gold-flash
 Material: LCP,UL94V-0
 Color: Natural(Beige)



Circuit No.	Dimensions			
	A	B	C	D
12P	22.00	30.00	24.75	26.52
14P	26.00	34.00	28.75	30.52

		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-23304126 传真: 0755-29940187						
		TITLE: PHA2.0卧贴 产品名称:		PART NO: C2022WR-nP 产品编号:				
X.X	±0.30	X.X*	±3*	APPD: 核准:	DATE	SCALE	UNIT	CODE NUMBER
X.XX	±0.20	X.XX*	±2*	CHECK: 王建业	2016-03-12	1:1	mm	A001
X.XXX	±0.10	X.XXX*	±1*	DRAW: 黄艳兰				