



环保物料

TEL:0769-82001899



PIN ASSIGNMENT:



*MATERIAL (IDC)

INSULATOR:PBT (UL 94V-0)

Contact: Copper Alloy.

Contact Plated: Gold or Tin over Nickel Plated.

*SPECIFICATIONS

TEMPERATURE RANGE: -20°C TO +105°C

CONTACT RESISTANCE: 3Ω MAX.

INSULATION RESISTANCE: 5MΩ MIN.

WITHSTANDING VOLTAGE: 300V 10S



OF TRANSPORT DIVISION:

序号	名称	规格说明	数量
1	端子	IDC-XP 二件式 (2.54mm)	2
2	电线	2651 28# 1.27间距灰排 7/0.12TS	20P
3	卡扣	反扣20P (2.54mm)	2

How to order :										
CL	254	X	X	XX	XXX	X	XX	X	X	X
Product Name: H:IDC F:FD CL:IDC Cable CLF:IDC+FD Cable	Pitch: 1:1.27mm 2:2.00mm 2.54mm	Number of Row: 1:Single Row 2:Double Row	Product Number: 1:Single 2:Two piece Type 3:Three Piece Type 4:with Battery buckle	NO OF Pins Per Row: 01~40P	Length of Cable: 0:No Cable XX:L=XXmm	Contact Plated: B:Half gold tin Q:ALL gold	Terminal Type: C:Common H:High tension S:Single contact Y:Double contact	Colour: 1:Black 2:Gray 3:Other	Cable Material: 0:Common 8:26#/0.16TS 8:28#/0.127TS	Packing: E:PE Bag P:Package T:Tube packing R:Roll packing

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan
				X.	±0.30 X° ±5°	CHKD	
				.X	±0.20 .X° ±2°	APPD	
				.XX	±0.08 .XX° ±1°		
				.XXX	±0.03 .XXX° ±0.5°	VIEW	⊕
AO	MODIFICATION	DRAW	DATE				
VER							

XFCN 兴飞连接器有限公司
XFCN CONNECTORS CO.,LTD.

PRODUCT NAME 灰排线两端IDC2.54/20P 三件式 L=190mm 不含头
PART. NO. CL2542320190BC10E

SHEET	1/1
DATE	2020.04.12
UNITS	mm
SCALE	1:1
DWG. NO.	009