



Technical Data Material
 Contact Material: Brass/Phosphor Bronze
 Contact plating: Nicker/Gold Flash
 Insulator Material: Black Polyester UL94V-0
 Standard: PBT

Electrical
 Current rating: 3.0amps/contact ma
 Contact resistance: 200m/contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding Voltage: 1000V AC/minute
 Mechanical
 Operating temperature: -40 C to +105C

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2014/8/18	M200D-02-035-B	
CHECKED			SHEET 1 OF 1	
APPROVALS			PROJ.	
TOLERANCES ARE		ANGLE	SCALE: 1:1	
30 ^{±0.15}	±0.30	±2°	1:1	
10 ^{±0.10}	±0.20			
5 ^{±0.05}	±0.15			

DEALON 德之隆®
 ELECTRONICS CO.,LTD
 DETECTOR SWITCHES