


P.C.B LAYOUT
BOTTOM VIEW

注：*a表示共模尺寸(7个)



8	CONTACT CLIP	PBS C5210R-EH	2	Ag CLAD																
7	TERMINAL	BRASS STRIP	6	Ag PLATED																
6	BASE	PHENOLIC RESIN	1	NATURAL																
5	FRAME	STEEL STRIP	1	Ni PLATED																
4	SCREEN	STEEL STRIP	1	Ni PLATED																
3	SPRING	STEEL WIRE	1	Ni PLATED																
2	BLOCK	STEEL STRIP	1	Ni PLATED																
1	KNOB	PA66	1	BLACK/RED																
NO.	PART NAME	MATERIAL	QTY	FINISHING																

TOLERANCE		UNLESS SPECIFIED		ANGULAR		NO		DATE		REVISIONS		BY		APPD	
UP TO 5mm: ±0.1		±1°		1											
ABOVE 5mm: ±0.2															

TITLE: TITLE : PUSH SWITCH
 MODEL: PS-22P02-N
 UNIT : MM
 SCALE: 1:1
 ROHS COMPLIANT
 DWN
 CHK'D
 APPD



PRO.AGI: REV :A0