





SCHEMATIC (NON-SHORTING)



P.C.B LAYOUT
BOTTOM VIEW

H=3.0mm

注：“*”表示关键尺寸(5个)

8					TOLERANCE									
7					UNLESS SPECIFIED									
6	SPRING PLATE	PBS STRIP	1	NATURAL	UP TO 5mm: ±0.1	ANGULAR	1							
5	CONTACT CLIP	PBS STRIP	1	Ag CLAD	ABOVE 5mm: ±0.2	±1°								
4	TERMINAL	BRASS STRIP	3	Ag PLATED			NO	DATE	REVISIONS		BY	APPD		
3	BASE	PHENOLIC RESIN	1	NATURAL	TITLE: SLIDE SWITCH			UNIT : MM	ROHS	DWN				
2	FRAME	STEEL STRIP	1	Ni PLATED	MODEL: SS-12D02			SCALE: 1:1	COMPLIANT	CHK'D				
1	KNOB	POM	1	BLACK	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD					
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:			REV :A0		