



H=XXmm

P.C.B LAYOUT  
BOTTOM VIEW

7	STEEL BALL	STEEL	1	NATURAL	TOLERANCE		UNLESS SPECIFIED			
6	SPRING	STEEL WIRE	1	NATURAL	UP TO 5mm: ±0.1	ANGULAR	A1	2020.4.23	更新图纸	
5	CONTACT	COPPER STRIP	1	Ag PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	XYZ
4	TERMINAL	BRASS STRIP	3	Ag PLATED	TITLE: VERTICAL SLIDE SWITCH		UNIT : MM	SCALE: 1:1	ROHS COMPLIANT	DWN
3	CASE	PA9T+94V0	1	BLACK	MODEL: SS-12D10				CHK'D	APPD
2	COVER	SUS	1	NATURAL	HAOYU(HONGKONG)LIMITED				APPD	
1	KNOB	PA66	1	BLACK	皓宇(香港)有限公司				PRO.AGL:	REV :A1
NO.	PART NAME	MATERIAL	QTY	FINISHING	HAOYU(HONGKONG)LIMITED				PRO.AGL:	REV :A1



HAOYU(HONGKONG)LIMITED  
皓宇(香港)有限公司