

PANEL CUT-OUT		
Z	Y	X
0.70~1.25	20.40~20.50	2.10~2.20
1.25~2.00	20.50~20.60	2.10~2.20
2.00~3.00	20.60~20.70	2.10~2.20

NOTES:

1.Rating:

KC 6(4)A 250VAC T85/55

VDE ENEC 6(4)A 250VAC T85/55

TUV 8A/128A 250VAC T85/55

UL CUL 6GPA 250VAC

10GPA 125VAC

TV-5 T105/55

CQC 6A 250VAC

6(8)A 250VAC

8A/128A 250VAC T105/55

2.Circuit Diagram:4P ON-OFF

3.Terminal Strength:≥80N

4.Electrical life:≥10000 cycles

5.Withstand Voltage:Withstand Voltage:1500VAC 1min


Terminals to Button:3000VAC 1min

Leakage Current:1mA

6.Current resistance:≤50mΩ (initial)

7.Insulation resistance:≥100MΩ

8.Body Materil:NYLON 66 94V-0~2



A4				普通公差:	深圳市华灿天禄电子有限公司							
A3				COMMON TOLERANCE :								
A2				UP TO 5	±0.20	单位	mm	投影	品名	跷板开关	比例	Free
A1				ABOVE 5 TO 30	±0.30	绘图	周金勇	核 对	梁金勇	型号	RS601D	
REV.	DATE	REVISION DESCRIPTION	ISSUE	ABOVE 30	±0.50	日期	2015.10.09	核 准	周培雷	图号	RS601D2-2010011BB	
				ANGULAR	±5°	DATE		APPROVAL BY		DWG NO.		