


Recommended PCB
Layout



Specifications:

规格:

- Voltage rating: 30V AC/DC
- 额定电压: 30V AC/DC
- Current rating: 3A AC/DC
- 额定电流: 3A AC/DC
- Withstanding voltage: 150V AC/minute
- 耐受电压: 150V AC/分钟
- Temperature range: -35°C~+85°C
- 温度范围: -35°C~+85°C
- Insulation resistance: 1000MΩ min
- 绝缘电阻: 1000MΩ Min
- Contact resistance: 100mΩ Max
- 接触电阻: 100mΩ Max

X0813 W V S - XX X -LP V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-06Pin-XXPin
- 6.High:A=0.48mm
Mating Height 0.6mm
- 7.Material:LP-LCP UL 94V-0 Black
- 8.Plating:V01-Gold Flash ;
SN-Tin Plating

X0813WVS-XXX-LPV01	LCP UL 94V-0	Copper Alloy	X0813F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

Δx	日期
Δx	日期
Δx	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5



DSND	SCALE: N/A
DWN	VIEW: [Symbol]
CHKD	UNIT: mm/in
APPD	SIZE: A4

MODEL TYPE: 0.8mm BTB Style Connector		
PART NO.: X0813WVS-XXX-LPV01		
DWG NO.: X-X0813WVS-XXX-LPV01		
WEIGHT	SHEET	REVISION
	1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED