





# RoHS

## SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au3U Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: LCP  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



## Ordering Information

1225 11 XX X N XX S XXX X 01

No. of Pins Per Row	Insulator Material Option	Contact Plating	Pin Length	Packing
1x40	A=BK-PBT	G0:0.8U" Gold		O=PE Bag
2x40	B=BK-PA66	G1:1U" Gold		A=Tray
3x40	C=BK-PA6T	G2:1.5U" Gold		T=Tube
1--40	D=BK-PA46	G3:2U" Gold		P=Tube+Cap
2--80	E=BK-PA9T	G4:3U" Gold		R=Reel+Cap
3--120	F=BK-LCP	G5:5U" Gold		M=Reel+Mylar
		S0:Gold Flash/Tin		
		SN:Tin		

Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

深圳市连盛精密连接器有限公司

PART NO. PH-00598

TITLE: 2.54PH H=2.5 1X3P DIP

OPERATION

DRAW

SCALE

FIT

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

APPROVE

SIZE

A4

X.XXX ±0.10

Angle ±3°

SHEET

1/1

DIM TOL

PROJ.

A0 2012.03.28 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION CHANGE