



| Part No | Pin | A | B | C | D |
|--------------------|-----|-------|-------|-------|-------|
| WAFER-MX1.25-2PWZ | 2 | 1.25 | 4.40 | 3.20 | |
| WAFER-MX1.25-3PWZ | 3 | 2.50 | 5.65 | 4.45 | |
| WAFER-MX1.25-4PWZ | 4 | 3.75 | 6.90 | 5.70 | 2.50 |
| WAFER-MX1.25-5PWZ | 5 | 5.00 | 8.15 | 6.95 | 3.75 |
| WAFER-MX1.25-6PWZ | 6 | 6.25 | 9.40 | 8.20 | 5.00 |
| WAFER-MX1.25-7PWZ | 7 | 7.50 | 10.65 | 9.45 | 6.25 |
| WAFER-MX1.25-8PWZ | 8 | 8.75 | 11.90 | 10.70 | 7.50 |
| WAFER-MX1.25-9PWZ | 9 | 10.00 | 13.15 | 11.95 | 8.75 |
| WAFER-MX1.25-10PWZ | 10 | 11.25 | 14.40 | 13.20 | 10.00 |
| WAFER-MX1.25-11PWZ | 11 | 12.50 | 15.65 | 14.45 | 11.25 |
| WAFER-MX1.25-12PWZ | 12 | 13.75 | 16.90 | 15.70 | 12.50 |
| WAFER-MX1.25-13PWZ | 13 | 15.00 | 18.15 | 16.95 | 13.75 |
| WAFER-MX1.25-14PWZ | 14 | 16.25 | 19.40 | 18.20 | 15.00 |
| WAFER-MX1.25-15PWZ | 15 | 17.50 | 20.65 | 19.45 | 16.25 |
| WAFER-MX1.25-16PWZ | 16 | 18.75 | 21.90 | 20.70 | 17.50 |

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| | | | | |
|---------------------------------------|-----------|---|---|---|
| MANUFACTURE DWG | |  |  东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd | |
| UNLESS OTHERWISE SPECIFIED TOLERANCES | | | TITLE: WAFER 1.25 弯针 | |
| DECIMALS: | ANGLES: | PAR | WAFER-MX1.25-NPWZ | |
| X.:±0.2 | X'.:±5° | DWN | | |
| .X:±0.1 | X.X':±3° | CHKD | | |
| .XX:±0.05 | X.XX':±1° | APVD | | |
| CUSTOMER COPY | | SCALE1:1 | UNIT:MM |  |
| | | SIZE:A4 | SHEET:1F1 | REV:A |