
DF005SA, DF01SA, DF02SA, DF04SA, DF06SA, DF08SA, DF10SA

www.vishay.com

Vishay General Semiconductor

Miniature Glass Passivated Single-Phase Surface-Mount Bridge Rectifiers



Case Style DFS

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS								
I _{F(AV)} 1 A								
V _{RRM}	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V							
I _{FSM}	30 A							
I _R	5 μΑ							
V _F at I _F = 1.0 A	1.1 V							
T _J max.	150 °C							
Package	DFS							
Circuit configuration	Quad							

FEATURES

- UL recognition, file number E54214
- Ideal for automated placement
- Middle surge current capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

General purpose use in AC/DC bridge full wave rectification for SMPS, lighting ballaster, adapter, battery charger, home appliances, office equipment, and telecommunication applications.

MECHANICAL DATA

Case: DFS

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: as marked on body

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)									
PARAMETER	SYMBOL	DF005SA	DF01SA	DF02SA	DF04SA	DF06SA	DF08SA	DF10SA	UNIT
Device marking code		DFA005S	DFA01S	DFA02S	DFA04S	DFA06S	DFA08S	DFA10S	
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward output rectified current at $T_A = 40 \ ^\circ C \ ^{(1)}$	I _{F(AV)}	I _{F(AV)} 1.0						А	
Peak forward surge current single half sine-wave superimposed on rated load	I _{FSM}	I _{FSM} 30						А	
Rating for fusing (t < 8.3 ms)	l ² t	l ² t 4.5						A ² s	
Operating junction and storage temperature range	TJ, T _{STG}	T _J , T _{STG} -55 to +150							°C

Note

⁽¹⁾ Units mounted on PCB with 0.51" x 0.51" (13 mm x 13 mm) copper pads

Revision: 09-Jul-2020

1



DF005SA, DF01SA, DF02SA, DF04SA, DF06SA, DF08SA, DF10SA

www.vishay.com

Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS	SYMBOL	DF005SA	DF01SA	DF02SA	DF04SA	DF06SA	DF08SA	DF10SA	UNIT
Maximum instantaneous forward voltage drop per diode	1.0 A	V _F				1.1				V
Maximum DC reverse current at rated DC	T _A = 25 °C	L				5.0				μA
blocking voltage per diode	T _A = 125 °C	IR	500							μ/ (
Typical junction capacitance per diode ⁽¹⁾		CJ				25				pF

Note

 $^{(1)}$ Measured at 1.0 MHz and applied reverse voltage of 4.0 V

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)									
PARAMETER	SYMBOL	OL DF005SA DF01SA DF02SA DF04SA DF06SA DF08SA DF10SA UN						UNIT	
Typical thermal resistance (1)	$R_{ extsf{ heta}JA}$	40							°C/W
Typical merma resistance (9	$R_{ ext{ heta}JL}$	15							

Note

⁽¹⁾ Units mounted on PCB with 0.51" x 0.51" (13 mm x 13 mm) copper pads

ORDERING INFORMATION (Example)									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
DF06SA-E3/45	0.386	45	50	Tube					
DF06SA-E3/77	0.386	77	1500	13" diameter paper tape and reel					

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Derating Curve Output Rectified Current





Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u> DF005SA, DF01SA, DF02SA, DF04SA, DF06SA, DF08SA, DF10SA

Vishay General Semiconductor



www.vishay.com

SHA'

Fig. 3 - Typical Forward Characteristics Per Diode




Fig. 4 - Typical Reverse Leakage Characteristics Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode





Fig. 6 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



Revision: 09-Jul-2020

Document Number: 88574

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.