


Circuit Diagram




NOTES:

1.ELECTCAL CHARACTERISTICS:

- 1-1.CONTACT CURRENT RATING: 50mA.
- 1-2.CONTACT VOLTAGE RATING: 12V. DC.
- 1-3.INSULATION RESISTANCE: 100 MΩ MIN.

2.MECHANICAL CHARACTERISTICS:

- 2-1.DURABILITY:100,000 CYCLES.
- 2-2.TRAVEL:0.20±0.10mm.



⑥	Dust cover	—	1	PI	Yellow	—
⑤	Terminal	—	2	Brass	Plating silver	—
④	Contact	—	1	F.Ag/SUS	Plating silver	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	—	—
①	Knob	—	1	PPA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS

DATE

DRAWN LIUCAN

2021.6.5

CHECKED

TITLE:

TACT SWITCHS

APPROVALS

PART NO.

K2-1851SN

TOLERANCES ARE

30~以上 ±0.30  
10~30 ±0.20  
5~10 ±0.15  
~ 5 ±0.10

ANGLE

UNIT: mm

SCALE: 1:1

PROJ:

DRAWING NO.

—

SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.

**HRD** 韓榮®

ELECTRONICS CO.,LTD