



Circuits	Dimensions (mm)			Circuits	Dimensions (mm)		
	A	B	C		A	B	C
PH1250-WT-02	1.25	3.10	7.50	PH1250-WT-12	13.75	15.60	20.10
PH1250-WT-03	2.50	4.35	8.80	PH1250-WT-13	15.00	16.85	21.30
PH1250-WT-04	3.75	5.60	10.00	PH1250-WT-14	16.25	18.10	22.55
PH1250-WT-05	5.00	6.85	11.30	PH1250-WT-15	17.50	19.35	23.80
PH1250-WT-06	6.25	8.10	12.60	PH1250-WT-16	18.75	20.60	25.05
PH1250-WT-07	7.50	9.35	13.80	PH1250-WT-17	20.00	21.85	26.30
PH1250-WT-08	8.75	10.60	15.00	PH1250-WT-18	21.25	23.10	27.55
PH1250-WT-09	10.00	11.85	16.30	PH1250-WT-19	22.50	24.35	28.80
PH1250-WT-10	11.25	13.10	17.60	PH1250-WT-20	23.75	25.60	30.05
PH1250-WT-11	12.50	14.35	18.80				

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO		DATE		REVISIONS		BY		APPD	
						UP TO 5mm: ± 0.1	ANGLES $\pm 1.5^\circ$										
						ABOVE 5mm: ± 0.2											
3	CONTACT FOOT		BRASS	XX	SN-PLATED	TITLE: CONNECTOR		UNIT : MM		ROHS		DWN					
2	CONTACT		BRASS	2	SN-PLATED	PART NO.: PH1250-WT-XX		SCALE: 2:1		COMPLIANT		CHK'D					
1	HOUSING		LCP	1		HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD					
								PRO.AGL:				REV :A0					