




客户确认	
日期	



Symbol 符号	Item 项目	Specification 规格
N	No. of Conductors (导体芯数)	12
P	Pitch (间距)	0.5±0.05
TP	Total Pitch (总间距)	5.5±0.10
W	Width (总宽度)	6.5±0.10
M	Margin (边缘宽度)	0.5±0.10
L	Total Length (总长度)	80±3
T	Insertion Thickness (插入厚度)	0.30±0.05
ST	Surface Thickness (线身厚度)	0.12±0.05
SI/S2	Conductor Strip Length (裸铜长度)	4/4±1.0
B1/B2	Supporting tape Length (补强板长度)	8/8±2.0
A1	Slanting (切口倾斜度)	<0.5

**ELECTRICAL CHARACTERISTICS**

Conductor Resistance: JISC-3102(at20°C) 2.20Ω/1M Max.  
Insulation Resistance: Apply the voltage of DC 500V for one min 100MΩ Min.

Dielectric Strength: Apply AC 500V for one minute.  
Continuity Test: Apply microtest machine No Open/Short  
Rated voltage & temperature:UL Sub. 758YV-1

**Material**

Insulation: Flame Retardant Polyester  
Color: White  
Conductor: Copper with 1u m min. tin-Plating  
Supporting Tape: Flame Retardant Polyester  
Color: Blue

核准:	日期:	 <b>深圳市灿科盟实业有限公司</b> CHANKEMENG INDUSTRYCO., LTD			
业务:	日期:	<b>品名规格:</b> FFC0.5-12P L=80MM 4/4-8/8 异面			
制图:	日期:	客户料号	C3025474	单位	mm
L Y F	2022-06-10	图纸编号	F-FFC0Z12P-0800	比例	/
			版本		A