




客户确认
日期



Symbol 符号	Item 项目	Specification 规格
N	No. of Conductors (导体芯数)	14
P	Pitch (间距)	1.0±0.05
TP	Total Pitch (总间距)	13.0±0.10
W	Width (总宽度)	15.0±0.10
M	Margin (边缘宽度)	1.0±0.10
L	Total Length (总长度)	100±3
T	Insertion Thickness (插入厚度)	0.30±0.05
ST	Surface Thickness (线身厚度)	0.12±0.05
SI/S2	Conductor Strip Length (裸铜长度)	4/4±0.5
B1/B2	Supporting tape Length (补强板长度)	8/8±1.0
A1	Slanting (绞口倾斜度)	<0.5

ELECTRICAL CHARACTERISTICS

Conductor Resistance: JISC-3102(at20°C) 2.20Ω/1M Max.
Insulation Resistance: Apply the voltage of DC 500V
for one min 100MΩ Min.

Dielectric Strength: Apply AC 500V for one minute.

Continuity Test: Apply microtest machine No Open/Short
Rated voltage & temperature:UL Sub. 758YV-1

Material

Insulation: Flame Retardant Polyester

Color: White

Conductor: Copper with 1u m min. tin-Plating

Supporting Tape: Flame Retardant Polyester

Color: Blue

核准:

日期:

业务:

日期:

制图:

LYF

日期:
2022-06-10

客户料号: C3025479
品名规格: FRC1.0-14P L=100mm 4/4-8/8 同面
深圳市灿科盟实业有限公司
CHANKEMENG INDUSTRY CO., LTD

单位	mm	比例	/	图例	⊕	▽
图纸编号	F-FRC1K14P-1000	版本	A			