



SPECIFICATIONS
 Current rating: 2A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20m Ω max.
 Withstand voltage: 800V AC/min
 Insulation resistance: 1000M Ω /min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.031"~0.063"(0.8~1.6)

Material:
 Part No: 4~40
 Insulator: Nylon 66 UL94V-0(2)
 Contact: Brass
 Finish: Au3u" Plated

Poles	Part No.	Dimension mm	
		A	B
4	2006R-2*2P	2.00	6.00
6	2006R-2*3P	4.00	8.00
8	2006R-2*4P	6.00	10.00
10	2006R-2*5P	8.00	12.00
12	2006R-2*6P	10.00	14.00
14	2006R-2*7P	12.00	16.00
16	2006R-2*8P	14.00	18.00
18	2006R-2*9P	16.00	20.00
20	2006R-2*10P	18.00	22.00
22	2006R-2*11P	20.00	24.00
24	2006R-2*12P	22.00	26.00
26	2006R-2*13P	24.00	28.00
28	2006R-2*14P	26.00	30.00
30	2006R-2*15P	28.00	32.00
32	2006R-2*16P	30.00	34.00
34	2006R-2*17P	32.00	36.00
36	2006R-2*18P	34.00	38.00
38	2006R-2*19P	36.00	40.00
40	2006R-2*20P	38.00	42.00

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

LYF

2016-08-28

TITLE:

2006R-2*9P 带定位 米白色 Au3u"

深圳市灿科盟实业有限公司
 CHANKEMENG INDUSTRY CO., LTD

CLIENT P/N /

UNIT mm SCALE free

FILE NO. S060800013 REV. B /