



RECOMMEND PCB LAYOUT
TOLERANCE: ± 0.05

- 技术指标:**
- 1、塑件表面应光洁、无毛刺、明显收缩、缺陷、裂纹等现象;
 - 2、温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 - 3、额定电压: 200V, AC, DC(等效);
 - 4、接触电阻: $\leq 30\text{m}\Omega$;
 - 5、绝缘电阻: $\geq 500\text{M}\Omega$;
 - 6、耐压: 1000V, AC/minute.

Poles	Part No	DIMENSIONS		
		DIW A	DIW B	DIW C
2	W-1251IN72P-0200	1.25	4.49	7.49
3	W-1251IN3P-0200	2.50	5.74	8.74
4	W-1251IN4P-0200	3.75	6.99	9.99
5	W-1251IN5P-0200	5.00	8.24	11.24
6	W-1251IN6P-0200	6.25	9.50	12.50
7	W-1251IN7P-0200	7.50	10.75	13.75
8	W-1251IN8P-0200	8.75	12.00	15.00
9	W-1251IN9P-0200	10.00	13.25	16.25
10	W-1251IN10P-0200	11.25	14.50	17.50
11	W-1251IN11P-0200	12.50	15.76	18.76
12	W-1251IN12P-0200	13.75	17.01	20.01
13	W-1251IN13P-0200	15.00	18.26	21.26
14	W-1251IN14P-0200	16.25	19.51	22.51
15	W-1251IN15P-0200	17.50	20.76	23.76
16	W-1251IN16P-0200	18.75	22.02	25.02

序号	零件名称	数量	材料	产地	镀层	备注
①	底座	1	LCP	中国		GP PASS
②	端子	N	黄铜	中国	镀底. 镀锡	GP PASS
③	焊片	2	黄铜	中国	镀底. 镀锡	GP PASS

TOLERANCE TABLE

.0	± 0.20
.00	± 0.10
.000	± 0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

SXA

2019-07-13

TITLE:

1251SMT-XP (立贴)

深圳市灿科盟实业有限公司
KIMT W CHANKLEMENT INDUSTRYCO., LTD

CLIENT P/N /

UNIT mm SCALE free

FILE NO. Ckwtw-1251-0037

REV. A JTXI