




技术要求:

1. 额定电负荷: DC 30V 0.5A;
2. 接触电阻: $\leq 0.06\Omega$;
3. 绝缘电阻: $\geq 100M\Omega$ (DC250V);
4. 耐压: 500VAC
5. 插力: 3-30N
6. 拔力: 3-30N
7. 寿命: 5,000



PJ-392B	PJ-392B-1	PJ-392B-2	PJ-392B-3	PJ-392B-4	PJ-392B-5	PJ-392B-6	PJ-392B-7	PJ-392B-8	PJ-392B-9	PJ-392B-10	PJ-392B-11

9	PJ392B 底座	PA46	1	BLACK								
8	PJ392B 4#弹片	SUS301	1	AU-PLATED	TOLERANCE				UNLESS SPECIFIED			
7	PJ392B 2#接触片	BRASS	1	AU-PLATED	UP TO 5mm: ± 0.1				ANGULAR $\pm 1^\circ$			
6	PJ392B 2#接触片	BRASS	1	AU-PLATED	ABOVE 5mm: ± 0.2				NO			
5	PJ392B 3#接触片	BRASS	1	AU-PLATED	TITLE: PHONE JACK				DATE			
4	PJ392B 1#接触片	BRASS	1	AU-PLATED	UNIT : MM				REVISIONS			
3	PJ392B 5#弹片	SUS301	1	AU-PLATED	MODEL: Pj-392B(HY)				SCALE: 3:1			
2	PJ392B 5#弹片	SUS301	1	AU-PLATED	HAOYU(HONGKONG)LIMITED				ROHS COMPLIANT			
1	PJ392B 5#弹片	SUS301	1	AU-PLATED	皓宇(香港)有限公司				CHK'D			
NO.	PART NAME	MATERIAL	QTY	FINISHING	PRO.AGI.				REV :A0			