



PIN	<del>φ2.0</del>	φ2.5
APPD.	✓	

注力度要求: 插力11N-20N, 拔力12-20N.  
(常规不带凹槽插头)

					CE	A3 2020.8.07 <sup>3</sup> 依据历史生产数据修正尺寸4.2至4.6	GYW		
						A2 2016.6.20 <sup>2</sup> 增加重点尺寸	liu		
						A1 2015.12.20 <sup>1</sup> 弹片增加骨位加大插拔力	liu		
6	DC005 PING	BRASS	1	Ni PLATED	ABOVE 5mm: ±0.2	NO	BY	APPD	
5	DC005 4#FLAT PIECE	BRASS	1	Ag PLATED					
4	DC005 2#CURVE PIECE	BRASS	1	Ag PLATED					
3	DC005Q 3#SPRING	SUS	1	Ag PLATED	TITLE:DC JACK		ROHS COMPLIANT	CHK'D	
2	DC005 COVER	PBT	1	YELLOW/BLACK/RED	MODEL:DC-005Q 2.0-SU				
1	DC005 CASE	PBT/PA66+PA6T	1	YELLOW/BLACK/RED	HAOYU(HONGKONG)LIMITED				
NO.	PART NAME	MATERIAL	QTY	FINISHING	皓宇(香港)有限公司		A		REV: A3