


SCHEMATIC



PIN	ø2.0	ø2.5	
APPD.			

					TOLERANCE								
					UNLESS SPECIFIED								
6	COVER	PBT			UP TO 5mm: ±0.1	ANGULAR	1						
5	CONTACT FOOT	BRASS	1	SN-Plating	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
4	PIN	H59 BRASS	1	Ni-Plating	TITLE:DC JACK			UNIT : MM	ROHS	DWN			
3	SPRING	STEEL	1	SN-Plating	MODEL:DC-016A 2.0-PU			SCALE: 6:1	COMPLIANT	CHK'D			
2	FLAT PIECE	H62 BRASS	1	SN-Plating	HAOYU (HONG KONG) LIMITED 皓宇(香港)有限公司						APPD		
1	HOUSING	PBT	1								PRO.AGL:		
NO.	PART NAME	MATERIAL	QTY	FINISHING									