


RECOMMENDED PCB LAYOUT



标记	版次	变更内容	日期
△	A版	新版图画	15-05-06
△	B版	物压口增加单边 0.20mm Max	20-03-26
△	C版	外壳宽度增加10.10mm规格	20-11-07

NOTE
 MATERIAL
 BODY&LATCH: NY66 RATED.
 NUMERAL CONTACTS: PHOSPHOR BRONZE
 SIMULATION CONTACTS: PHOSPHOR BRONZE
 GROUND CONTACT: BRASS
 SHELL: ZINC ALLOY
 LEGS: BRASS
 RIVET: BRASS
 CONTACT PLATING: GOLD PLATING OVER NICKEL
 ELECTRICAL SPECIFICATION
 CURRENT RATING: 1.5A;
 VOLTAGE RATING: 40V;
 CONTACT RESISTANCE: 30mΩ MAX.
 INSULATION RESISTANCE: 1000MΩ MIN 500V DC.
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC
 ENVIRONMENTAL
 OPERATING TEMPERATURE: -20°C~80°C.
 ○ MARK IS MAJOR TEST DIMENSION.
 PART NO. DESCRIPTION:

38 4-29 2 2 Z A 20 15
 SERIES NO.:
 PRODUCT KIND:
 PIN NUMBER:
 FEMALE:
 NUT TYPE: 1=NO LOCK NUT
 2=LOCK NUT, 3=ADD NUT

38 4-29 2 2 Z A 20 15
 SERIAL NUMBER
 COLOR CODE: 01=WHITE
 20: OYSTER WHITE
 PLATING CODE: A=1'u' B=3'u'
 SHELL KIND: Z=ZINC ALLOY

NO.	NUT SPC	NO.	NUT SPC
1	4.75*11.80 L=4.80	1	4.75*11.80 L=4.80
2	4.75*11.80 L=5.80	2	4.75*11.80 L=5.80
3	4.75*13.00 L=4.80	3	4.75*13.00 L=4.80
4	4.75*13.00 L=5.80	4	4.75*13.00 L=5.80

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	CHECKED:	DATE:	DRAWN:	DATE:
				LYP	2015-05-06

深圳市灿科盟实业有限公司
 CANTW CHANKLEMENT INDUSTRY CO., LTD
 TITLE: DVT24+5 母座锁螺丝(锌合金) 弯插
 PROD. P/N: C3025484
 UNIT: mm SCALE: free
 FILE NO.: D-DVT10R24P-F000 REV. C SY000