







标记	版次	变更内容	日期
▲	A版	新版图面	2011-01-13
▲	B版	设计变更, 焊片2.45修改为1.75mm	2017-10-06

材料 Material

接触件 (Contact) : 磷青铜±0.25mm 镀亮锡
 Phosphor Bronze Tin-plated
 焊片 (solder tab): 磷青铜 ±0.20mm 镀亮锡
 Phosphor Bronze Tin-plated
 塑胶主体 (Housing) : LCP耐热树脂
 (UL94V-0) Heat resistance plastic (UL94V-0)
 铆条 (Slider) : PPS耐热树脂
 (UL94V-0) Heat resistance plastic (UL94V-0)

技术参数 SPECIFICATIONS

间距 (Pitch) : 1.0
 极数 (Poles) : 3~40
 额定电压 (Voltage rating) : 50V
 额定电流 (Current rating) : 0.5A
 耐压值 (Withstand Voltage) : 500V
 工作温度 (Working Temperature) : -25℃~+85℃
 绝缘电阻 (Insulation Resistance) : ≥500MΩ
 接触电阻 (Contact Resistance) : ≤30mΩ



孔位	A	B	C	孔位	A	B	C
3	10.00	4.10	2.00	22	29.00	23.10	21.00
4	11.00	5.10	3.00	23	30.00	24.10	22.00
5	12.00	6.10	4.00	24	31.00	25.10	23.00
6	13.00	7.10	5.00	25	32.00	26.10	24.00
7	14.00	8.10	6.00	26	33.00	27.10	25.00
8	15.00	9.10	7.00	27	34.00	28.10	26.00
9	16.00	10.10	8.00	28	35.00	29.10	27.00
10	17.00	11.10	9.00	29	36.00	30.10	28.00
11	18.00	12.10	10.00	30	37.00	31.10	29.00
12	19.00	13.10	11.00	31	38.00	32.10	30.00
13	20.00	14.10	12.00	32	39.00	33.10	31.00
14	21.00	15.10	13.00	33	40.00	34.10	32.00
15	22.00	16.10	14.00	34	41.00	35.10	33.00
16	23.00	17.10	15.00	35	42.00	36.10	34.00
17	24.00	18.10	16.00	36	43.00	37.10	35.00
18	25.00	19.10	17.00	37	44.00	38.10	36.00
19	26.00	20.10	18.00	38	45.00	39.10	37.00
20	27.00	21.10	19.00	39	46.00	40.10	38.00
21	28.00	22.10	20.00	40	47.00	41.10	39.00

APPROVED: _____ DATE: _____

CHECKED: _____ DATE: _____

DRAWN: Jul1-Liu DATE: 2017-10-06

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

TITLE: FPC1.0-4P 下接 抽拉式

深圳市灿科盟实业有限公司
 Ckmtw CHANKLEMENT INDUSTRYCO., LTD

PROD. P/N	C3025533	UNIT	mm	SCALE	free
FILE NO.	F-FPC1M04P-B310	REV.	A	LX00	