



BOARD PAD HOLE
 Recommended PCB Layout
 General Tolerance ±0.05mm



NOTE :

- Material:
 - Housing: High Temperature Thermoplastic, LCP, Color: Black, UL94V-0
 - Terminal and Switch: Phosphor Bronze, T=0.15mm
- Plating:
 - Contact Area: Gold 1μ"
 - Solder Area: Gold Flash.
 - Underplating: Ni overall 50μ" min.
- Specification:
 - Contact Current Rating: 0.5A
 - Dielectric Withstanding Voltage: AC500V r.m.s.
 - Insulation Resistance: 1000 MΩ Minimum, at DC 500V.
 - Contact Resistance: 100 mΩ Maximum.
 - Mating Cycle: 100,000 Insertions.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 全塑SIM CARD 8+2P 0.45H
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW315-SIM10-045B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO. _____
			DRAW NO: HYC-2206021145
			SHEET NO. 1 OF 1