



技术要求:

- 1: 产品插拔力10-20N.
- 2: 盐雾测试48H.
- 3: 接触电阻<70毫欧.
- 4: "\*"重点尺寸.
- 5: 产品外观无电镀脱皮, 红胶不满等不良.

				TOLERANCE		A2	2017.04.11	重点尺寸1.7改为1.5		GYW
				UNLESS SPECIFIED		A1	2017.03.16	增加产品技术要求		GYW
				UP TO 5mm: ±0.1	ANGULAR	A0	2017.03.03	首次发行		GYW
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY APPD
5	DC086 COVER	EPOXY RESIN	1	RED	TITLE:DC JACK		UNIT : MM	ROHS COMPLIANT	DWN	
4	DC086 INSULATOR	PA66	1	BRACK	MODEL:DC-086-2.1-PU		SCALE: 4:1	CHK'D		
3	DC086 φ2.1PIN	BRASS	1	80-120U" Ni PLATED	<b>HAOYU(HONGKONG)LIMITED</b> 皓宇(香港)有限公司		APPD		PRO.AGL:   REV :A2	
2	DC086 SHELL	BRASS	1	80-120U" Ni PLATED						
1	DC086 SPRING TERMINAL	PHO-BRONZE	1	80-120U" Ni PLATED						
NO.	PART NAME	MATERIAL	QTY	FINISHING						