



P.C.B LAYOUT

SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 2P2T
4. Contact Resistance:  $\leq 70m\Omega$ MAX
5. Operating Force:  $130\pm 30gf$ ,  $200\pm 80gf$
6. Life test: 10,000 cycles

KNOB X=2, 3, 4, 4.3mm

G2: 柄长2mm  
B: 胶柄黑色

				TOLERANCE							
				UNLESS SPECIFIED		A1	2016.12.26	修正BOM信息		GYW	
				UP TO 5mm: $\pm 0.1$	ANGULAR	A0	2014.4.25	初版		Liu	
				ABOVE 5mm: $\pm 0.2$	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD
4	MK22D10 SPRING	PBS	2	NATURAL	TITLE:MINI SLIDE SWITCH		UNIT : MM	ROHS	DWN		
3	MK22D14C CASE	PA6T/0.3mm BRASS STRIP	1	BLACK/Ag PLATED	MODEL: MK-22D14CG2-B弹线		SCALE: 7:1	COMPLIANT	CHK'D		
2	MK22D10 COVER	0.15mm SUS	1	WASHING	 <b>HAOYU(HONGKONG)LIMITED</b> 皓宇(香港)有限公司		APPD		PRO.AGL: 		REV :A1
1	MK22D10 KNOB	PA66/PA6T	1	WHITE/BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING							