



P.C.B LAYOUT

G2 : 柄长2mm
B: 胶柄黑色

SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 2P4T
4. Contact Resistance: $\leq 70m\Omega$ MAX
5. Operating Force: 200gf-350gf
6. Life test: 10,000 cycles

				TOLERANCE UNLESS SPECIFIED		A2	2018.1.25	原MK22D10弹线改为MK23D38弹线	PWJ	
				UP TO 5mm: ±0.1	ANGULAR	A1	2017.05.31	客诉力度重至430, 修改力度管控标准为	GYW	
				ABOVE 5mm: ±0.2	±1°	A0	2017.05.17	初版	GYW	
						NO	DATE	REVISIONS	BY	APPD
5	MK24D02 TERMINAL	BRASS	1	Ag PLATED	TITLE:MINI SLIDE SWITCH		UNIT : MM	ROHS COMPLIANT	DWN	
4	MK23D38 SPRING	PBS $\phi 0.25$ mm	2	WASHING	MODEL: MK-24D02G2-B弹线		SCALE: 5:1	CHK'D		
3	MK24D02 CASE	PA6T	1	BLACK	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司		APPD			
2	MK24D02 COVER	SUS	1	WASHING			PRO.AGL:		REV :A2	
1	MK24D02 KNOB	PA6T/PA46	1	BLACK						
NO.	PART NAME	MATERIAL	QTY	FINISHING						