




P.C.B LAYOUT



SPECIFICATION

1. Rating: DC 12V 0.3A
 2. Travel: 2 mm
 3. Function: 1P2T
 4. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
 5. Operating Force: 130±30gf, 200±80gf
 6. Life test: 10,000 cycles
- KNOB X=2, 3, 4, 5, 6mm

G2: 胶柄长2mm
B: 胶柄黑色

				TOLERANCE UNLESS SPECIFIED								
				UP TO 5mm: ±0.1	ANGULAR ±1°	A1	2021.6.15	△ 新增外观拨柄要求		CYW		
				ABOVE 5mm: ±0.2		A0	2017.4.13	初版		PWJ		
						NO	DATE	REVISIONS		BY APPD		
4	MK22D10 CONTACT/SPRING	BERYLLIUM/PBS	1	Ag PLATED/NATURAL	TITLE:MINI SLIDE SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	MS12D17 CASE	PA9T/0.3mm BRASS STRIP	1	BLACK/Ag(Ni) PLATED	MODEL:MS-12D17G2-B弹线			SCALE: 6:1	COMPLIANT	CHK'D		
2	MS22D16 COVER	0.2mm SUS	1	WASHING	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD	
1	MS22D16 KNOB	PA46/PA9T	1	WHITE/BLACK							PRO.AGL:	
NO.	PART NAME	MATERIAL	QTY	FINISHING								