




P.C.B LAYOUT



SCHEMATIC



SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 1.5 mm
3. Function: 2P2T
4. Contact Resistance: ≤70mΩMAX
5. Operating Force: 200±80gf
6. Life test: 10,000 cycles

KNOB X=1, 1.5, 1.7, 2.0, 4.0mm

G2: 胶柄长2mm
B: 胶柄黑色

					TOLERANCE							
					UNLESS SPECIFIED							
					UP TO 5mm: ±0.1	ANGULAR	1	2017.4.13	初版			pwj
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
5	MS22C01 SPRING PLATE	0.15mm SUS	1	NATURAL	TITLE:MINI SLIDE SWITCH			UNIT : MM	ROHS	DWN		
4	MS23C01 CONTACT	BERYLLIUM	2	Ag PLATED	MODEL:MS-22C01G2.0-B			SCALE: 8:1	COMPLIANT	CHK'D		
3	MS22C01 CASE	PA6T/LCP/6# BRASS STRIP	1	BLACK/Ag PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD		PRO.AGL:		REV :A0
2	MS22C01 COVER	0.15mm SUS	1	WASHING								
1	MS22C01 KNOB	PA6T/PA66/LCP	1									
NO.	PART NAME	MATERIAL	QTY	FINISHING								