


SPECIFICATION

- 1. Rating: DC 6V 0.3A
- 2. Travel: 2 mm
- 3. Function: 2P3T
- 4. Contact Resistance: ≤70mΩ MAX
- 5. Operating Force: 200±80gf, 300±100gf
- 6. Life test: 10,000 cycles

KNOB G=1.8, 2.0, 3.0, 4.0 5.0mm
T=6.5, 7.5, 10.5mm



G2: 胶柄长2mm
B: 胶柄颜色黑色

				TOLERANCE UNLESS SPECIFIED									
				UP TO 5mm: ±0.1	ANGULAR	A1	2017.01.09	新增T6.5规格		GYW			
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
4	MK23D38 SPRING	PBS	2	NATURAL	TITLE:MINI SLIDE SWITCH		UNIT : MM	ROHS	DWN				
3	MS23D18 KNOB	PA46/PA9T	1	BLACK	MODEL:MS-23D20 G2-B 弹线		SCALE: 6:1	COMPLIANT	CHK'D				
2	MS23D18 COVER	0.2mm SUS	1	WASHING	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD	
1	MS23D20 CASE	PA9T/9# BRASS STRIP	1	BLACK/Ag PLATED								PRO.AGL:	
NO.	PART NAME	MATERIAL	QTY	FINISHING									