



- SPECIFICATION**
1. Rating: DC 12V 0.3A
 2. Travel: 2 mm
 3. Function: 4P2T
 4. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
 5. Operating Force: $200\pm 80\text{gf}$
 6. Life test: 10,000 cycles

Knob X=2, 3, 4, 5mm
Terminal Z=6.0, 7.5mm

G2: 胶柄长2mm
B: 胶柄黑色

				TOLERANCE								
				UNLESS SPECIFIED		A1	2018.10.19	修改胶柄材质为PA46		GYW		
				UP TO 5mm: ±0.1	ANGULAR	A0	2017.03.27	初版		GYW		
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
4	MS42D02 CONTACT	BERYLLUM COPPER	4	Ag PLATED	TITLE:MINI SLIDE SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	MS42D20 CASE	PA6T/LCP/0.3mm BRASS	1	BLACK/Ag PLATED	MODEL:MS-42D20G2-B			SCALE: 5:1		CHK'D		
2	MS42D02 COVER	SUS	1	Ni PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD		
1	MS42D02 KNOB	PA46	1	BLACK						PRO.AGL:		
NO.	PART NAME	MATERIAL	QTY	FINISHING								