


P.C.B LAYOUT



SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 2P4T
4. Contact Resistance: $\leq 70m\Omega$ MAX
5. Operating Force: 200gf-350gf
6. Life test: 10,000 cycles

				TOLERANCE							
				UNLESS SPECIFIED		A1	2018.03.15	更新PCB开孔图		GYW	
				UP TO 5mm: ±0.1	ANGULAR	A0	2018.03.06	首次发行		GYW	
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
5	MK24D02 TERMINAL	BRASS	1	Ag PLATED	TITLE:MINI SLIDE SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
4	MK23D38 SPRING	PBS $\phi 0.25$ mm	2	WASHING	MODEL: MS-24D02G2-B弹线		SCALE: 5:1	CHK'D			
3	MK24D02 CASE	PA6T	1	BLACK	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司		APPD				
2	MS24D02 COVER	SUS	1	WASHING							
1	MS24D02 KNOB	PA46	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:		REV :A1