

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

J

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

E4

REVISED

ECR-15-003916

11MAR2015

TS

KB

NOTES;

△ MUST BE KEPT BETWEEN **-Z-** AND 2mm
 2 THE MATING CAP HSG. PART NUMBER; 175444, 175448
 3 APPLIED CONTACT P/N 173630, 173631
 4 APPLICABLE PRODUCT SPEC NO. 108-5280

注:

△ **-Z-**面より2mmの範囲で測定
 2. 嵌合相手ハウジング型番: 175444, 175448
 3. 内装するリセパタクルコンタクト型番は173630, 173631
 4. 適用製品規格番号 108-5280

OBSOLETE	淡灰 (LIGHT GRAY)	6-175442-6
	灰色 (GRAY)	175442-6
OBSOLETE	青 (BLUE)	175442-5
	白 (WHITE)	175442-1
	色 (COLOR)	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.KADOSAKI 16JUN2005		
DIMENSIONS: 単位: 耗 mm		CHK T.SHINOHARA 16JUN05		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD K.BETSUI 16JUN05	NAME 名称	
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 製品規格	12Pos. PLUG HOUSING .040/.070 HYBRID I/O CONN. (POWER)	
MATERIAL 材料 PBT		FINISH 仕上	APPLICATION SPEC 取付適用規格	12極 プラグハウジング .040/.070 ハイブリッド I/O コネクタ (パワー用)
一般公差 (GENERAL TOLERANCE) 0<math> \leq $10 : \pm 0.2$ 10<math> \leq $30 : \pm 0.25$ 30<math> \leq $100 : \pm 0.3$ ANGLES : $\pm 3^\circ$		WEIGHT	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO 番号 C=175442	RESTRICTED TO -
		SCALE 尺度 2:1	SHEET 1 of 1	REV E4

1470-19 (3/11)