


P.C.B LAYOUT

DC-002	DC-002-1
4	4
5	5
3	3

SCHEMATIC

MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	φ1.0	φ1.3	φ1.65
APPD.	✓		



					TOLERANCE UNLESS SPECIFIED							
6	PING	BRASS	1	Ni PLATED	UP TO 5mm: ±0.1	ANGULAR		2013.9.3	依据ECN1309001	huli		
5	3#SPRING	PBS/SUS	1	Ag PLATED	ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY	APPD	
4	5#CURVE PIECE	BRASS	1	Ag PLATED	TITLE:DC JACK			UNIT : MM	ROHS COMPLIANT	DWN		
3	4#FLAT PIECE	BRASS	1	Ag PLATED	MODEL: DC-002 1.0			SCALE: 5:1	CHK'D			
2	COVER	PBT	1	BLACK	HAoyu(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD				
1	CASE	PBT/PA9T	1	BLACK				PRO.AGL:	REV : A			
NO.	PART NAME	MATERIAL	QTY	FINISHING								