





HAOYU



P.C.B LAYOUT

PIN	φ1.0	φ1.3	φ1.65
APPD.			

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm: ±0.1	ANGULAR	A0	2018.4.4	初版		GYW		
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY APPD		
5	DC033 PING	BRASS	1	Ni PLATED	TITLE:DC JACK			UNIT : MM	ROHS COMPLIANT	DWN			
4	DC033A 5#CURVE PIECE	BRASS	1	Ag PLATED	MODEL: DC-033A 1.65			SCALE: 6:1		CHK'D			
3	DC033A 4#FLAT PIECE	BRASS	1	Ag PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD		
2	DC033A 3#SPRING	SUS	1	Ag PLATED									
1	DC033A CASE	PBT	1	BLACK							PRO.AGL:		REV :A0
NO.	PART NAME	MATERIAL	QTY	FINISHING									