



P.C.B. LAYOUT

SPECIFICATION

1. Rating: DC 12V 0.3A
2. Function: 2P2T
3. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
4. Operating Force: $180\pm 80\text{gf}$, $250\pm 100\text{gf}$
5. Life test: 10,000 cycles

S: 自锁

E: 操作力 $250\pm 100\text{gf}$

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm: ± 0.1	ANGULAR	1							
					ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD		
5	CAM STICK	SUS	1	NATURAL	TITLE: VERTICAL PUSH SWITCH			UNIT : MM	ROHS COMPLIANT	DWN				
4	SPRING	SUS	1	NATURAL	MODEL: PB-22E60PA-S-E			SCALE: 5:1	CHK'D					
3	CASE	PA66/0.3mm BRASS	1	GREY/Ag PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
2	COVER	PA66	1	BLACK								PRO.AGL:		
1	KNOB	PA66/0.045mm PBS	1	WHITE/BLACK/Ag CLAD										
NO.	PART NAME	MATERIAL	QTY	FINISHING										