

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
AO		NEW		21.12.15

NOTES1:

UL Standard

- 1.Rated voltage/current : 150V / 8A
- 2.Withstanding voltage : AC1250V/1Min.

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 2.54mm, Poles : N=04~48P
- 3.Operating temperature: -40°C~+105°C
- 4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						
TO	Over	TO	Over	TO	Over	TO	Over	0.1/10
6	6 TO 10	30	30 TO 60	60	60 TO 100	100	100 TO 150	∠
±0.15	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30		±2'

5.RoHS Compliance

Ordering Information






JL15EDGRHD-254 XX B 0 1

Pitch
254=2.54PH

No.of pins
4P~48P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Packing
O=Pe bag
T=Tube
A=Tray



PCB LAYOUT

DRAW	SHUANGPING ZHENG	SCALE	FIT	东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		UNIT	mm		
CHECK	LICHAO LIU	SIZE	A4	PART NO.	JL15EDGRHD-254XXB01
		SHEET	1/1	TITLE:	JL15EDGRHD-THR-2.54-2XNP插拔式公座/弯针/黑色
APPROVE	YONGLIANG GAO	PROJ.			