


PIN	φ2.0	φ2.5	φ2.7
APPD			



P.C.B LAYOUT

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ±0.1	ANGULAR ±1°	A0	2016.12.30	首次发行		GYW	
				ABOVE 5mm: ±0.2		NO	DATE	REVISIONS		BY	APPD
6	DC005 PING	BRASS	1	Ni PLATED	TITLE:DC JACK		UNIT : MM	ROHS COMPLIANT	DWN		
5	DC015 3#SPRING	SUS/PBS	1	Ag PLATED	MODEL:DC-015 2.0-PU		SCALE: 3:1	CHK'D			
4	DC015 2#CURVE PIECE	BRASS	1	Ag PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司		APPD				
3	DC015 5#FLAT PIECE	BRASS	1	Ag PLATED			PRO.AGL:		REV :A0		
2	DC015 BASE	PHENOLIC RESIN	1	NATURAL							
1	DC015 CASE	PBT	1	BLACK/WHITE							
NO.	PART NAME	MATERIAL	QTY	FINISHING							