



RoHS&REACH

ECN NO.	DESCRIPTION	DATE
A-1	修改外形及尺寸	2020.11.14
A-2	更新图面细节	2021.11.20




材料Material:


- 外壳材质: PBT, PA66, PA46 (UL 94V-0)
Housing Material: PBT, PA66, PA46 (UL 94V-0)
- 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter Phosphor Bronze; Gold Plating Over Nickel

电气Electrical

- 额定电压: 交流125伏
Voltage Rating: 125 VAC Rms
- 额定电流: 1.5安培
Current Rating: 1.5 AMP
- 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX
- 绝缘电阻: 直流500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V DC
- 绝缘耐压: 交流60Hz 1000V下, 1分钟
Dielectric Withstanding Resistance: 1000V AC Rms 60Hz. 1Min
- 耐久: 插拔750次以上
Durability: 750 Cycles Min
- 工作温度: -40°C ~ +85°C
Operation Temperature: -40°C ~ +85°C



PCB LAYOUT
(Top View)



5201 - X X X X X X

Positions	Contacts	Panel	Plastic	Color	Gold Plating
8	2/4/6/8	0-w/0 Panel 1-w/Panel	1-PBT 2-PA66 3-PA46	1-Black 2-Gray 3-Other	1-G/Fu" 2-3u" 3-6u" 4-15u" 5-30u" 6-50u"

未注公差		设计	X.C.S	比例	1:1
尺寸标注	公差				
X.	±0.25 ±2.0°	审核		单位	mm
.X	±0.20 ±1.5°				
.XX	±0.15 ±1.0°	批准		图幅	A4
.XXX	±0.10 ±0.5°				
		角法		版本	A-2
				图数	第1页 共1页

H 恒连电子科技有限公司
EVERCOM ELECTRONIC TECHNOLOGY CO., LTD
<http://www.chinarj45.com>

产品型号 5201 8P8C 有边
产品编号 5201-881XXX
图纸编号 HL2152A8802